


CORIO CD Heating Immersion Circulator

The new generation of laboratory circulators

In addition to the advantages of the CORIO C Circulator, the CORIO CD Immersion Circulator can be equipped with an optional pump set for temperature control of external applications.

Your advantages

- Precise temperature control
- For internal and external applications (accessories required)
- For bath tanks with a max. filling volume of 50 liters
- Bright, white, easy to read display
- Very quiet
- Easy operation
- Easy pump change-over between internal and external circulation
- USB connection
- Class III (FL) according to DIN 12876-1



● Pump capacity (Water)

Technical Data

Order No.	9012000
Model series	CORIO
Category	Heating Immersion Circulators
Working temperature range (°C)	+20 ... +150
Temperature stability (°C)	±0.03
Setting / display resolution	0.01 – 0.1 °C
Temperature Display	LED
Heating capacity (kW)	2
Pump capacity flow rate (l/min)	15
Pump capacity flow pressure (bar)	0.35
Ambient temperature	5...40 °C
Dimensions W x L x H (cm)	13.2 x 16 x 36.2
Weight (kg)	2.6
Cooling coil	optional
Usable immersion depth (cm)	16.6
Available voltage versions	230 V / 50 Hz 208 V - 230 V / 60 Hz 115 V / 60 Hz 100 V / 50-60 Hz

Characteristics



100% Checked.
100% testing. 100% quality. Each CORIO undergoes thorough quality testing before leaving the factory.



Locked in.
The lockable power plug guarantees safe connection. More process safety.



ATC.
Absolute Temperature Calibration, 1-point calibration (CD).



Modern. Reliable.
Every JULABO Circulator is equipped with high-grade components like i.e. platinum sensors, proven motor technology, CAN-Bus communication and much more.



Brilliant.
Bright display with strong illumination can be viewed easily from a long distance.



Quick start.
Individual JULABO consultation and comprehensive manuals at your disposal.



Connection. Easy.
Inclined pump connections (M16x1) facilitate the connection of applications. Each unit includes 2 barbed fittings of 8/12 mm diameter each.



Safety.
CORIO CD complies with Class III (FL) according to DIN 12876-1 and switches off automatically in case of high temperature or low liquid level alarm.



Everything at the front.
All operating controls and safety functions are accessed easily and comfortably from the front.



Satisfied customers.
11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



Green technology.
Development consistently applied environmentally friendly materials and technologies.



Services 24/7.
Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at www.julabo.com.



Internal. External.
The pump is controlled via a lever located directly below the display. Easily change between internal and external circulation.



Switch on. And off you go.
Intelligent operating concept. Ready for operation with just a few quick and easy steps.



JULABO. Quality.
Highest standards of quality for a long product life.



USB.
Remote control made easy. CORIO CD circulators feature a USB connection.

Refer to www.julabo.com for more information regarding the entire JULABO product portfolio.

Technical changes without prior notification. Images may deviate from the original. For applications near or below ambient temperature: use a cooling coil or JULABO immersion cooler.